UNIT CLOSED CIF	╛	VADCO	TNIC	evapco	DWG	WLETM1806-DI		-	
MODEL # eco-LSWE 10-3M	18-Z SCALE NTS		VAPCO,	TIAC.		SERI	AL #	DATE ₁₁	1/26/2025
NOTES: 1. (M)- FAN MOTOR LOCA' 2. MPT DENOTES MALE P FPT DENOTES FEMALE BFW DENOTES BEVELE GVD DENOTES GROOV FLG DENOTES PLAIN EN 3. +UNIT WEIGHT DOES N ACCESSORIES (SEE AC 4. 3/4" [19mm] DIA. MOUNT RECOMMENDED STEEL 5. DIMENSIONS LISTED AC 6. * - APPROXIMATE DIME USE FOR PRE-FABRICA 7. HEAVIEST SECTION IS 8. MAKE-UP WATER PRES 20 psi [137 kPa] MIN, 50 9. SERIES FLOW PIPING AD DRAIN ARE BY OTHERS	IPE THREAD PIPE THREAD PIPE THREAD ED FOR WELDING ED OT INCLUDE CESSORY DRAWINGS) FING HOLES. REFER TO SUPPORT DRAWING FOLLOWS: ENGLISH F [METRIC] [NSIONS DO NOT TION OF CONNECTING COIL SECTION ESURE PSI [344 kPa] MAX IND AUX. CROSSOVER	mm]	FACE B PLAN VIEW	9'-9 3/4"		FACE C		FACI	<u>E D</u>
2'-6 3/ [772 SERIES FLC		[44	-9" * 148] *			18'-1/- [5493 FACE A	4"		
PIPI (BY OTHER 1'-10 1/4" * 1	OOR———————————————————————————————————		2" [50] MPT 8'-6 [20	12'-7 5/8" [3851]	(4) 1/2" [15] FPT VENT AUX. CROSSOVER DRAIN (BY OTHERS				
2'-7 1/2" [800] 2'-7 3/ [806 3'-7 1/ [1099 4'-1 7/ [1267	4"	3" [80] MPT DRAIN 9'-9 3/4" [2991]	2'-1/8" [613]	2'-		18'-1/c [5493			
FACE B									
SHIPPING 22110 WEIGHT) lbs+ [10030] kg+	OPERATING WEIGHT	31860 lbs+ [14455] kg+	HEAVIEST SEC WEIGHT	TION 14820 lbs+ [6725	5] kg+	NO. OF SHIPPING SECTIONS	2 DRAWN BY:	TLS