UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-LSWE 10-6M36-Z	SCALE NTS

EVAPCO, INC. Evapeo

DWG. # WLETM3612-DRD-SF REV. SERIAL # DATE_11/26/2025

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END
- 3. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 4. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TÓ RECOMMENDED STEEL SUPPORT DRAWING
- 5. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT IN [METRIC] [mm]
- 6. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. HEAVIEST SECTION IS COIL SECTION
- 8. MAKE-UP WATER PRESSURE
- 20 psi [137 kPa] MIN, 50 psi [344 kPa] MAX 9. SERIES FLOW PIPING AND AUX. CROSSOVER
- DRAIN ARE BY OTHERS

FACE C



