UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 4-4F9






DWG. # REV. WB3040908-DRE-ST SERIAL # DATE_{12/13/2025}

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]


FACE C


PLAN VIEW



FACE D

FACE A





DRAWN BY: **SHIPPING** OPERATING HEAVIEST SECTION NO. OF SHIPPING SECTIONS 5520 lbs+ [2505] kg+ 7910 lbs+ [3590] kg+ 4850 lbs+ [2200] kg+ WEIGHT WEIGHT WEIGHT