UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 9-6M14

EVAPCO, INC. Evapco




DWG. # REV. WB3091412-DRC-ST DATE_{12/13/2025} SERIAL #

DRAWN BY: SLR


NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]





FACE A





NO. OF SHIPPING SECTIONS **SHIPPING OPERATING** HEAVIEST SECTION 19370 lbs+ [8790] kg+ 21450 lbs+ [9730] kg+ 29720 lbs+ [13485] kg+ WEIGHT WEIGHT WEIGHT