

|                               |              |                                                                                                            |                            |                   |
|-------------------------------|--------------|------------------------------------------------------------------------------------------------------------|----------------------------|-------------------|
| UNIT<br>CLOSED CIRCUIT COOLER |              | <div>EVAPCO, INC.</div>  | DWG. #<br>WB3171410-DRD-ST | REV.<br>-         |
| MODEL #<br>eco-ATWB 17-5L14   | SCALE<br>NTS |                                                                                                            | SERIAL #                   | DATE<br>2/15/2026 |


  

NOTES:

- (M)- FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END
- +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
METRIC [mm]

FACE C




FACE D

FACE B

PLAN VIEW


FACE A



FACE B



FACE A

|                 |                        |                  |                        |                         |                       |                          |   |           |     |
|-----------------|------------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|-----------|-----|
| SHIPPING WEIGHT | 37580 lbs+ [17050] kg+ | OPERATING WEIGHT | 52820 lbs+ [23960] kg+ | HEAVIEST SECTION WEIGHT | 16710 lbs+ [7580] kg+ | NO. OF SHIPPING SECTIONS | 4 | DRAWN BY: | SLR |
|-----------------|------------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|-----------|-----|