UNIT	CLOSED CIRCUIT COOLER		EVADCO	TRIC EV	apco	DWG. # WB3121806-DRC-ST		REV
MODEL #			EVAPCO, INC. Evapeo			SERIAL #		DATE 11/8/2025
2. HEAN 3. MPT FPT II BFW GVD FLG PE D 4. +UNI ACCE 5. MAKI 20 ps 6. *-APF FOR PIPIN 7. 3/4" [RECO	FAN MOTOR LOCATION VIEST SECTION IS UPPER SEC DENOTES MALE PIPE THREA DENOTES FEMALE PIPE THREA DENOTES BEVELED FOR WE DENOTES GROOVED DENOTES FLANGE ENOTES PLAIN END T WEIGHT DOES NOT INCLUE ESSORIES (SEE ACCESSORY E-UP WATER PRESSURE IS MIN [137 KPA], 50 PSI MAX [34 PROXIMATE DIMENSIONS DO PRE-FABRICATION OF CONNI	ND EAD ELDING DE DE DRAWINGS) 44 kPa] NOT USE ECTING S. REFER TO DRAWING.		FACE B PLAN VIEW		ACE C ACCESS DOOR FACE A	FACE D	
	1'-10 1/4" * (2) 4" [10] E 2" [50] MPT — (2) 4" [100] E 2" [50] MPT — (2) 4" [100] E 2" [50] MPT — (2) 4" [100] E 3" [80] DRAIN [92] — 51/4 [133] 41/4 [108]	J MPT OVERFLOW 4" 3]	7" [178] 3'-3/8" * [924] * 8'-3 5/8" [2532] 14'-5 7/8" [4416] 6'-2 1/4" [1884] 1'-5" [433]	1'-3 1/4" [387]]] [(2) 1/2" [15] FPT VENT				

SHIPPING WEIGHT 24310 lbs+ [11030] kg+ OPERATING WEIGHT 37240 lbs+ [16895] kg+ HEAVIEST SECTION WEIGHT 20390 lbs+ [9250] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: SLR

FACE A

11'-10" [3607]