JNIT CLOSED CIRCUIT COOLER		EVAPCO, INC. Evapco			DWG. # WB3122806-DRC-ST	REV.
MODEL # eco-ATWB 12-3K28	SCALE NTS	EVAPC	O, INC.		SERIAL #	DATE <sub>12/13/2025</sub>
NOTES:  1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER S 3. MPT DENOTES MALE PIPE THRE FPT DENOTES FEMALE PIPE TH BFW DENOTES BEVELED FOR V GVD DENOTES GROOVED FLG DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT INCL ACCESSORIES (SEE ACCESSOF 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 KPa], 50 psi MAX [ 6. *-APPROXIMATE DIMENSIONS D FOR PRE-FABRICATION OF CON PIPING 7. 3/4" [19mm] DIA. MOUNTING HOL RECOMMENDED STEEL SUPPOI 8. DIMENSIONS LISTED AS FOLLO' ENGLISH FT-IN METRIC [mm]	EAD READ READ VELDING  UDE RY DRAWINGS)  344 kPa] O NOT USE INECTING LES. REFER TO RT DRAWING.	PLA	FACE B N VIEW	ACCESS DOOR  FAC	ACCESS DOOR	FACE D
1'-10 1/4" * (4) 4" [100] BFW (565] * (4) 4" [100] BFW (4) 4" [100] BFW (4) 4" [100] BFW (4) 4" [100] BFW (564)	FLUID IN FLUID OUT O 15	8'-3 5/8" [ 2532 ] 15'-5 7/8" [ 4721 ]	1'-3 1/4" [ 387 ]  (4) 1/2" [15] FPT VENT  1'-4 3/4" [ 425 ]	13'-11 3/4"  [ 856  FAC		1'-4 3/4" [ 425]