

UNIT	CLOSED CIRCUIT COOLER		EVAPCO, INC.  [®]	DWG. #	WB3242008-DRC-ST	REV.
MODEL #	eco-ATWB 24-4M20	SCALE NTS		SERIAL #		DATE 2/9/2026

- NOTES:
- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. -*APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]



DWG. # WB3242008-DRC-ST


REV.

SERIAL #

DATE 2/9/2026

FACE C


(2) ACCESS DOOR



FACE B
PLAN VIEW

FACE D

FACE A



**SHIPPING
WEIGHT**

64330 lbs+ [29180] kg+

**OPERATING
WEIGHT**

96000 lbs+ [43545] kg+

HEAVIEST SECTION WEIGHT

37650 lbs + [13545] kg +

NO. OF SHIPPING SECTIONS

4

DRAWN BY: SLD