UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 3-3C3-Z

EVAPCO, INC. evapco




DWG. # REV. WB3030306-DRE-SF DATE 11/21/2025 SERIAL #

## NOTES:


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** [METRIC] MM


## **FACE C**

**FACE B PLAN VIEW** 



## **FACE A**





DRAWN BY: NO. OF SHIPPING SECTIONS **SHIPPING** OPERATING HEAVIEST SECTION 1470 lbs+ [670] kg+ 2050 lbs+ [930] kg+ 1190 lbs+ [540] kg+ WEIGHT WEIGHT WEIGHT