




UNIT		CLOSED CIRCUIT COOLER		<div>EVAPCO, INC.</div> <div><div>evapco</div></div>	DWG. #		WB36M1206-DRC-ST		REV.		-								
MODEL #		eco-ATWB 20-3M12			SCALE		NTS		SERIAL #		DATE		9/15/2025						
<div>NOTES:</div> <div>1. (M)- FAN MOTOR LOCATION</div> <div>2. HEAVIEST SECTION IS UPPER SECTION</div> <div>3. MPT DENOTES MALE PIPE THREAD</div> <div> FPT DENOTES FEMALE PIPE THREAD</div> <div> BFW DENOTES BEVELED FOR WELDING</div> <div> GVD DENOTES GROOVED</div> <div> FLG DENOTES FLANGE</div> <div> PE DENOTES PLAIN END</div> <div>4. +UNIT WEIGHT DOES NOT INCLUDE</div> <div> ACCESSORIES (SEE ACCESSORY DRAWINGS)</div> <div>5. MAKE-UP WATER PRESSURE</div> <div> 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]</div> <div>6. *-APPROXIMATE DIMENSIONS DO NOT USE</div> <div> FOR PRE-FABRICATION OF CONNECTING</div> <div> PIPING</div> <div>7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO</div> <div> RECOMMENDED STEEL SUPPORT DRAWING.</div> <div>8. DIMENSIONS LISTED AS FOLLOWS:</div> <div> ENGLISH FT-IN</div> <div> METRIC [mm]</div>																			
<div>FACE B</div> <div>PLAN VIEW</div> <div></div> <div>FACE B</div>					<div>FACE C</div> <div>(2) ACCESS DOOR</div> <div></div> <div>FACE D</div> <div>FACE A</div> <div></div> <div>FACE A</div>														
SHIPPING WEIGHT		29740 lbs+ [13490] kg+		OPERATING WEIGHT		44760 lbs+ [20305] kg+		HEAVIEST SECTION WEIGHT		12310 lbs+ [5585] kg+		NO. OF SHIPPING SECTIONS		4		DRAWN BY:		SLR	