

UNIT	CLOSED CIRCUIT COOLER		EVAPCO, INC. 	DWG. #	WB36M2412-DRC-ST	REV.
MODEL #	eco-ATWB 20-6L24	SCALE NTS		SERIAL #		DATE 2/11/2026

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. -*APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]




DWG. # WB36M2412-DRC-ST

SERIAL #

REV.

DATE 2/11/2026



Face A

This technical drawing illustrates the front view of a double-decker bus, specifically Face A. The bus features a two-door entrance on the left side, with each door accompanied by a small rectangular window. The lower deck is characterized by a series of eight rectangular, honeycomb-patterned grilles. The upper deck is visible above the roofline. The drawing includes several dimension lines: a height dimension of 1'5" [432] for the upper deck, a height dimension of 1'5" [432] for the lower deck, and a total width dimension of 24'2" [7366] at the bottom. The front of the bus is marked with a vertical arrow pointing upwards, and the rear is marked with a vertical arrow pointing downwards.

FACE B

SHIPPING WEIGHT 90660 lbs+ [41125] kg+ OPERATING WEIGHT 128560 lbs+ [58315] kg+ HEAVIEST SECTION WEIGHT 19960 lbs+ [9055] kg+ NO. OF SHIPPING SECTIONS 6 DRAWN BY: SLR