


UNIT	CLOSED CIRCUIT COOLER		
MODEL #	eco-ATWB 20-6N36	SCALE	NTS

# EVAPCO, INC.


DWG. #	WB36M3612-DRC-ST	REV.	-
SERIAL #		DATE	2/11/2026

NOTES:


1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE  
PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. -\*APPROXIMATE DIMENSIONS DO NOT USE  
FOR PRE-FABRICATION OF CONNECTING  
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO  
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:  
ENGLISH FT-IN  
METRIC [mm]



## **FACE B**



**FACE B**  
**PLAN VIEW**



## **FACE A**

SHIPPING WEIGHT 132400 lbs+ [60060] kg+ OPERATING WEIGHT 189720 lbs+ [86060] kg+ HEAVIEST SECTION WEIGHT 29280 lbs+ [13285] kg+ NO. OF SHIPPING SECTIONS 6 DRAWN BY: SLR