


UNIT	CLOSED CIRCUIT COOLER		 [®]	DWG. #	WB3121210-DRC-SF	REV.
MODEL #	eco-ATWB 12-5N12-Z	SCALE NTS		SERIAL #	DATE	2/18/2026

NOTE

1. (M) - FAN MOTOR LOCATION
2. HEAVIEST SECTION IS UPPER SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
4. + UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE SEPARATE DRAWINGS
FOR ACCESSORIES)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. -* APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
7. SERIES FLOW PIPING AND AUX. CROSSOVER
DRAIN BY OTHERS
8. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
9. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN	METRIC [mm]
---------------	-------------


ENGLISH FT-IN
METRIC [mm]




FACE B



DWG. #	WB3121210-DRC-SF	REV.	-
SERIAL #		DATE	2/18/2026



FACE B



FACE A

SHIPPING WEIGHT 23480 lbs+ [10655] kg+ OPERATING WEIGHT 33720 lbs+ [15300] kg+ HEAVIEST SECTION WEIGHT 20770 lbs+ [9425] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: JLG