UNIT MODEL #	CLOSED CIRCUIT COOLER		EVAPCO, INC. Evapeo		DWG. # WB3121406 SERIAL #	DATE 11/8/2025
NOTES: 1. (M) - F 2. HEAV 3. MPT I FPT E BFW GVD I FLG E PE DE 4. + UNI ACCI FOR 5. MAKE 20 psi 6. * - AP FOR I PIPIN 7. SERIE DRAII 8. 3/4" [RECC	FAN MOTOR LOCATION //IEST SECTION IS UPPER SE DENOTES MALE PIPE THRE/ DENOTES FEMALE PIPE THRE DENOTES BEVELED FOR WI DENOTES GROOVED DENOTES FLANGE ENOTES PLAIN END IT WEIGHT DOES NOT INCLU ESSORIES (SEE SEPARATE I ACCESSORIES) E-UP WATER PRESSURE I MIN [137 KPa], 50 psi MAX [3 PROXIMATE DIMENSIONS D PRE-FABRICATION OF CONN	CCTION AD EAD ELDING JDE DRAWINGS 44 kPa] O NOT USE JECTING CROSSOVER ES. REFER TO T DRAWING.		FACE B AN VIEW	FACE C ACCESS DOOR	FACE D
	(4) 4" [100] BFW FLUID IN 1'-10 1/4" * [565] 2" [50] MPT MAKE-UP	5'-9 1/4" *	3'-3/8" * [924] * [2532] (4) 4" [100] BFW FLUID OUT 13'-11 7/8" [4264]	11-3 1/4" [387] (4) 1/2" [15] FPT VENT SERIES FLOW PIPING (SEE NOTE 7) AUX. CROSSOVER DRAIN (SEE NOTE 7)	FACE A	

2'-1 1/4"
[643]

3" [80] MPT
DRAIN
OVERFLOW

11'-5"
[133]

4 1/4"
[108]

7'-2"
[2184]

11'-10"
[3607]

FACE B

FACE B

NO. OF SHIPPING SECTIONS 2 DRAWN BY: JLG