UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 9-3H9-Z

EVAPCO, INC. Evapea





DWG. # REV. WB3090906-DRC-SF DATE<sub>12/14/2025</sub> SERIAL #


## NOTES:

- 1. (M) FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. + UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES)
- MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \* APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER **DRAIN BY OTHERS**
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS:

**ENGLISH FT-IN** METRIC [mm]







**SHIPPING** WEIGHT

9460 lbs+ [4295] kg+

OPERATING WEIGHT

13450 lbs+ [6105] kg+

HEAVIEST SECTION WEIGHT

8020 lbs+ [3640] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG