UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 24-5L14-Z

EVAPCO, INC. Evapeo


DWG. # REV. WB3241410-DRC-SF DATE 11/21/2025 SERIAL #

NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]



FACE C




FACE D

FACE B PLAN VIEW

5'-9 1/4' [1759] 3'-3/8" [924] (8) 4" [100] BFW FLUID IN 9'-8 5/8' [2964] (8) 4" [100] BFW 3'-3 1/4" * [997] FLUID OUT 16'-10 7/8" [5153] 6" [**154**] 7'-2 1/4' [2189] 4'-8" [1422] (2) 2" [50] MPT 11'-4 3/4" [3473] (2) 3" [80] MPT -DRAIN 11'-5 3/4' [3499] (2) 3" [80] MPT OVERFLOW 11'-10" [3607] 24'-1 1/8' [7344] **FACE B**

FACE A



SHIPPING 53200 lbs+ [24135] kg+ WEIGHT

OPERATING WEIGHT

77160 lbs+ [35000] kg+

HEAVIEST SECTION WEIGHT

23540 lbs+ [10680] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG