UNIT	CLOSED CIRCUIT C	OOLER
MODEL #	eco-ATWB 9-5H18-Z	SCALE NTS

EVAPCO, INC. evapco

DWG. # REV. WB3091810-DRC-SF DATE_{11/22/2025} SERIAL #


NOTES:

- 1. (M) FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. + UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES)
- 5. MAKE-UP WATER PRESSURE
- 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING **PIPING**
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER **DRAIN BY OTHERS**
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS:


ENGLISH FT-IN METRIC [mm]




FACE C



FACE A





SHIPPING 24530 lbs+ [11130] kg+ WEIGHT

OPERATING WEIGHT

34380 lbs+ [15595] kg+

HEAVIEST SECTION WEIGHT

21740 lbs+ [9865] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY: JLG