UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 24-6L14-Z

EVAPCO, INC. Evapco

REV. WB3241412-DRC-SF

SERIAL #

DATE<sub>11/21/2025</sub>


## NOTES:

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]




## **FACE C**


DWG. #



**FACE B PLAN VIEW** 

FACE D





DRAWN BY: JLG NO. OF SHIPPING SECTIONS

**SHIPPING** WEIGHT

61300 lbs+ [27810] kg+

OPERATING WEIGHT

87140 lbs+ [39530] kg+

HEAVIEST SECTION WEIGHT

27590 lbs+ [12515] kg+