




UNIT CLOSED CIRCUIT COOLER	EVAPCO, INC. 	DWG. # WB3171412-DRD-SF	REV. -
MODEL # eco-ATWB 17-6M14-Z	SCALE NTS	SERIAL #	DATE 4/9/2026
NOTES: (M)- FAN MOTOR LOCATION - HEAVIEST SECTION IS UPPER SECTION - MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE PE DENOTES PLAIN END +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) - MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING - SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. - DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm] FACE C  FACE D FACE B PLAN VIEW  FACE A 			
SHIPPING WEIGHT 42900 lbs+ [19460] kg+	OPERATING WEIGHT 59440 lbs+ [26965] kg+	HEAVIEST SECTION WEIGHT 19370 lbs+ [8790] kg+	NO. OF SHIPPING SECTIONS 4 DRAWN BY: JLG