UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 12-5L14-Z	SCALE NTS





DWG. # REV. WB3121410-DRC-SF DATE 11/11/2025 SERIAL #

NOTES:

SHIPPING

WEIGHT

- 1. (M) FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. + UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING **PIPING**
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN**



FACE B

HEAVIEST SECTION

WEIGHT

PLAN VIEW

ACCESS DOOR


FACE C

23540 lbs+ [10680] kg+

FACE D

DRAWN BY: JLG

NO. OF SHIPPING SECTIONS



38580 lbs+ [17500] kg+

OPERATING

WEIGHT

26600 lbs+ [12070] kg+