

UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 12-5L18-Z	SCALE NTS




DWG. #	WB3121810-DRC-SF	REV.	-
SERIAL #		DATE	2/18/2026

NOTES:


- (M) - FAN MOTOR LOCATION
- HEAVIEST SECTION IS UPPER SECTION
- MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
- + UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE SEPARATE DRAWINGS
FOR ACCESSORIES)
- MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- * - APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
- SERIES FLOW PIPING AND AUX. CROSSOVER
DRAIN BY OTHERS
- 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
- DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN
METRIC [mm]



FACE B


PLAN VIEW



FACE C

ACCESS DOOR

FACE D



FACE A