UNIT	CLOSED CIRCUIT COOLER		EVAPCO, INC.		DWG. #	DWG. # WB3121810-DRC-SF	
MODEL #	eco-ATWB 12-5M18-Z	SCALE NTS	EVAPCO	, INC.	SERIAL #		DATE <sub>11/11/2025</sub>
2. HÉAVI 3. MPT D FPT DI BFW D GVD D FLG DI PE DE 4. + UNIT ACCE FOR P FOR P PIPINO 7. SERIE DRAIN 8. 3/4" [19 RECOI	AN MOTOR LOCATION EST SECTION IS UPPER SEC ENOTES MALE PIPE THREAD ENOTES FEMALE PIPE THREAD ENOTES BEVELED FOR WEI ENOTES GROOVED ENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLUD SSORIES (SEE SEPARATE DI CCCESSORIES) UP WATER PRESSURE WIN [137 KPa], 50 psi MAX [34-4-4-4-4-4-4-4-4-4-4-4-4-4-4-4-4-4-4-	DAD LDING  DE RAWINGS  4 kPa] NOT USE CTING  ROSSOVER  5. REFER TO DRAWING.	[ 7" ]	FACE B PLAN VIEW  1'-3 1/4" [ 387 ]	FACE C ACCESS DO	FACE D	•
	(4) 4" [100] BFW FLUID IN 3'-3 1/4" * [ 997]	5'-9 1/4" *	3'-3/8" * [ 924] * [ 2964]  (4) 4" [100] BFW FLUID OUT  15'-10 7/8" [ 4848]	(4) 1/2" [15] FPT VENT  SERIES FLOW PIPING (SEE NOTE 7)			
	0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	[80] MPT AAIN OVERF 133]  [44" 51/4"	6' * 6'-2 1/4" [ 1884] 1'-5" [ 433] 1 HOW	AUX. CROSSOVER DRAIN (SEE NOTE 7)			
	-	11'-10" [ 3607]		1'-11 1/8" — <b>—</b>		-	
		FACE B			FACE A		