JNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 12-3K36-7	SCALE NTS



DWG. # WB3123606-DRC-SF REV.
SERIAL # DATE 11/8/2025

DRAWN BY: JLG

NO. OF SHIPPING SECTIONS

NOTES:


SHIPPING

WEIGHT


- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS UPPER SECTION
- 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]

FACE C

FACE B PLAN VIEW



FACE A



HEAVIEST SECTION

WEIGHT

20390 lbs+ [9250] kg+

OPERATING

WEIGHT

74480 lbs+ [33785] kg+

48620 lbs+ [22055] kg+