INIT	CLOSED CIRCUIT COOLER		EVAPCO, INC. Evapco			DWG. # WB3	3123610-DRC-SF	REV.
IODEL #	eco-ATWB 12-5L36-Z	SCALE NTS	EVAPC	O, INC		SERIAL #		DATE <sub>11/11/2025</sub>
2. HEAV 3. MPT [ FPT [ FPT C BFW   GVD I FLG C PE DE 4. +UNIT ACCE 5. MACE 20 psi 6. *-APP FOR F PIPIN 7. SERIE DRAIN 8. 3/4" [1 RECC	AN MOTOR LOCATION IEST SECTION IS UPPER S DENOTES MALE PIPE THRE IENOTES FEMALE PIPE THI DENOTES BEVELED FOR W DENOTES GROOVED IENOTES FLANGE ENOTES PLAIN END WEIGHT DOES NOT INCLU SSORIES (SEE ACCESSOR UP WATER PRESSURE MIN [137 KPa], 50 psi MAX [ ROXIMATE DIMENSIONS DI PRE-FABRICATION OF CON G ES FLOW PIPING AND AUX. I BY OTHERS.  9mm] DIA. MOUNTING HOL IMMENDED STEEL SUPPOR ISIONS LISTED AS FOLLOW ENGLISH FT-IN METRIC [mm]	EAD READ READ /FLDING  JDE Y DRAWINGS)  344 kPa] O NOT USE NECTING  CROSSOVER  ES. REFER TO RT DRAWING.	F. PLAN V.	ACE B IEW	ACCESS DOO	ACE C	ACCESS DOOR	FACE D
3'-3 1/ [ 997	2" [50] MPT — MAKE-UP	(8) 4" [100] BFW FLUID OUT  6" *  [154] *  (2) 3" [80] M OVERFLOW	AUX. CR 7'-2 1/4" [ 2189 ]	1'-3 1/4" [ 387 ]  (8) 1/2" [15] FPT VENT  ES FLOW PIPING (SEE NOTE 7)  OSSOVER DRAIN (SEE NOTE 7)  1'-11 1/8" [ 587]	18'-0" [ 5486 ]	2 1/2" [ 64] — 36'-2 1/2" — 11036]	1'-11 1/8" _	
	FACE				<u> </u>	ACE A		

HEAVIEST SECTION WEIGHT

29780 lbs+ [13510] kg+

SHIPPING WEIGHT OPERATING WEIGHT

98160 lbs+ [44525] kg+

67400 lbs+ [30575] kg+

DRAWN BY: JLG

NO. OF SHIPPING SECTIONS