UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 7-5J9-Z

EVAPCO, INC. Evapco

WEIGHT


DWG. # REV. CW4C070910-DRA-SF DATE<sub>11/22/2025</sub> SERIAL #


TAM

## NOTES:

WEIGHT

- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS FAN/CASING SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE
- 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. \*-APPROXIMATE DIMENSIONS DO NOT USE
- FOR PRE-FABRICATION OF CONNECTING
- 7. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.
- 8. 3/4" [19MM] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 9. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]





WEIGHT

