| UNIT CLOSED CIRCUIT COOLER | | | · · · · · · · · · · · · · · · · · · · | | | DWG. # CW4C071810-DRA-SF | | REV. |
|--|---|--|---|--|----------|--------------------------------|-----------|----------------------------|
| 10DEL # | eco-ATWB 7-5H18-Z | SCALE NTS | EVAPO | CO, INC. 📮 | evapco | SERIAL # | | DATE _{12/14/2025} |
| 2. HEAV 3. MPT I FPT I BFW GVD I FLG I PE DI 4. +UNIT ACCE 5. MAKE 20 psi 6. *-APF PIPIN 7. SERIE DRAII 8. 3/4" [RECC 9. DIME | AN MOTOR LOCATION IEST SECTION IS FAN/CASIN DENOTES MALE PIPE THREADENOTES BEVELED FOR WEDENOTES GROOVED DENOTES FLANGE ENOTES PLAIN END TWEIGHT DOES NOT INCLUITS SORIES (SEE ACCESSORY E-UP WATER PRESSURE MIN [137 KPa], 50 psi MAX [3- ROXIMATE DIMENSIONS DO PRE-FABRICATION OF CONN | AD EAD ELDING DE ' DRAWINGS) 44 kPa] NOT USE JECTING CROSSOVER S. REFER TO T DRAWING. | | FACE B PLAN VIEW | ACCESS D | FACE A | ACCESS DO | |
| 2" [5 2" [5 | 100] BFW | (4) | 2'-11 3/8" [899] 1'-10 7/8" * 4" [100] BFW FLUID OUT 5'-3 7/8" [1622] 13'-3 1/2" [4051] - 51/4" * [1530] - 3" [80] MPT OVERFLOW | SERIES FLOW PIPING (SEE NOTE 7) AUX. CROSSOVER DRAIN (SEE NOTE 7) | | | | |
| | -, 7'- □ 22: FAC | 4" 35] E B | | 1'-4 7/8" | • | - 18'-0" [5486] FACE A | | |

HEAVIEST SECTION WEIGHT

19220 lbs+ [8720] kg+

NO. OF SHIPPING SECTIONS

DRAWN BY:

TAM

SHIPPING WEIGHT OPERATING WEIGHT

29010 lbs+ [13160] kg+

22240 lbs+ [10090] kg+