UNIT **CLOSED CIRCUIT COOLER** MODEL # NTS eco-ATWB 7-6J36

EVAPCO, INC. evapco



DWG. # REV. CW4C073612-DRA-ST DATE<sub>12/14/2025</sub> SERIAL #

DRAWN BY:


TAM


## NOTES:

**SHIPPING** 

WEIGHT

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS FAN/CASING SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING **GVD DENOTES GROOVED** FLG DENOTES FLANGE PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. \*-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH FT-IN** METRIC [mm]






50940 lbs+ [23110] kg+

OPERATING

WEIGHT

65980 lbs+ [29930] kg+



**FACE A** 

22450 lbs+ [10185] kg+

HEAVIEST SECTION

WEIGHT

NO. OF SHIPPING SECTIONS