
UNIT	CLOSED CIRCUIT COOLER		
MODEL#	eco-ATWB 7-4J14-Z	SCALE	NTS

EVAPCO, INC. Evapeo


CW4C071408-DRA-ST	REV	-
SERIAL#	DATE:	12/14/2025

NOTES

- 1. (M)- FAN MOTOR LOCATION
- 2. HEAVIEST SECTION IS FAN/CASING SECTION
- 3. MPT DENOTES MALE PIPE THREAD
 FPT DENOTES FEMALE PIPE THREAD
 BFW DENOTES BEVELED FOR WELDING
 GVD DENOTES GROOVED
 FLG DENOTES FLANGE
 PE DENOTES PLAIN END
- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- *-APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
- 7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
- 8. DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN METRIC [mm]




FACE C



FACE D

JLG

FACE A



FACE B FACE A

SHIPPING WEIGHT 14740 lbs+ [6690] kg+ OPERATING WEIGHT 19320 lbs+ [8765] kg+ HEAVIEST SECTION WEIGHT 12550 lbs+ [5695] kg+ OPERATING WEIGHT 2550 l