CLOSED CIRCUIT CO  MODEL # eco-ATWB 14-6K14  NOTES	Inou F	TS	EVAPCO, I	INC. 🖺	apco	CW4C141412-DRB-ST	
NOTES				_		SERIAL#	DATE: 11/15/2025
NOTES  1. (M)- FAN MOTOR LOCATIC 2. HEAVIEST SECTION IS FA 3. MPT DENOTES MALE PIPE FPT DENOTES FEMALE PIPE FPT DENOTES FEMALE PIPE BFW DENOTES BEVELED GVD DENOTES FLANGE PE DENOTES PLAIN END 4. +UNIT WEIGHT DOES NOT ACCESSORIES (SEE ACCE 5. MAKE-UP WATER PRESSL 20 psi MIN [137 kPa], 50 psi 6. *-APPROXIMATE DIMENSIFOR PRE-FABRICATION OPIPING 7. 3/4" [19mm] DIA. MOUNTIN RECOMMENDED STEEL S 8. DIMENSIONS LISTED AS F ENGLISH FT-IN METRIC [mm]	N/CASING SECTETHREAD PE THREAD FOR WELDING  INCLUDE ESSORY DRAWI JRE MAX [344 kPa] DNS DO NOT US F CONNECTING G HOLES. REFE UPPORT DRAWI OLLOWS:	INGS) SE SE SER TO SING.	11 40 7/m *	FAC PLAN		FACE C  (M)  ACCESS DOOR  ACCESS DOOR  (M)  FACE A	FACE D
3" [76] 6		(8) 4*[100] BFW FLUID NI  (8) 4*[100] BFW FLUID OUT	(2) 3" [80] MPT	993]	1'-2" [355] (8) 1/2" [15] FPT VENT	ACCESS (M) (M) (M) (13'-11 3/4"	
6	-11 3/4" [2127] 7'-4" [2235] 15'-1 [460 FACE	DRAIN _5 1/8" _[130] 1/8" _1]	50100 lbs+ [22725] kg+	HEAVIEST SECTION WEIGHT	[435]	[4261]  FACE A  NO. OF SHIPPING SECTIONS 4	DRAWN BY: JLG