### ### ### ### ### ### ### ### ### ##	CLOSED CIRCUIT COOLER			EVADCO	TNC	evapco	DWG. # CW4C141406-DRB-ST	REV -
WOTES (PAN MOTOR) LOCATION (SANCASING SECTION) METORICON IS FANCASING SECTION) METORICON IS FANCASING SECTION (SANCE PIECE	MODEL#	eco-ATWB 14-3J14-Z	NTS	LVAPCO	, 114C. =		SERIAL #	
1'-7 1/2" [495] 1'-7 1	2. HÉAVIES 3. MPT DEN FPT DEN BFW DEN GVD DEN FLG DEN PE DENO 4. +UNIT WE ACCESSO 5. MAKE-UP 20 psi MIN 6. *-APPRO FOR PRE PIPING 7. 3/4" [19mm RECOMM 8. DIMENSIO	T SECTION IS FAN/CASIN IOTES MALE PIPE THREA OTES FEMALE PIPE THREA OTES FEMALE PIPE THREA IOTES BEVELED FOR WE IOTES GROOVED OTES FLANGE ITES PLAIN END EIGHT DOES NOT INCLUE ORIES (SEE ACCESSORY WATER PRESSURE IN [137 kPa], 50 psi MAX [34 XIMATE DIMENSIONS DO-FABRICATION OF CONN IDIA. MOUNTING HOLE: IENDED STEEL SUPPORTONS LISTED AS FOLLOWS ENGLISH FT-IN	D EAD ELDING DE DRAWINGS) 14 kPa] NOT USE ECTING S. REFER TO DRAWING.			ACE B IN VIEW	(M) ACCESS DOOR CCCESS DOOR (M)	FACE D
FACE D		5] * (M) (d) 4" [100] SFW (d) 4" [100] SFW (e) 4" [100] SFW (e) 4" [100] SFW (e) 4" [210] SFW (e) 4" [2105] 6" -11 3/4" [2127] 7" -4"	[1073] (4) # [100] SFW (5) # [100] SFW (4) # [100] SFW (4) # [100] SFW (5) # [100] SFW (6) # [100] SFW (7) [130] 15'-1 1/8" [4601]	[581] 2'-11 3/8" [899] 4'-0 7/8" [1241] 12'-6 1/4" [133] 5'-6 1/4" [1683] 2" [50] MPT (E-UP OVERFLOW	2" [3822]	(4) 1/2" [15] FPT VENT	ACCESS DOOR DOOR DOOR 13'-11 3/4" [4261]	
	SHIPPING WEIGHT	24980 lbs+ [11335] kg+		G 32980 lbs+ [14960] kg+	HEAVIEST SECTION WEIGHT	10300 lbs+ [4675] kg+	NO. OF SHIPPING SECTIONS 4	DRAWN BY: JLG