

UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 7-5K28	SCALE NTS

EVAPCO, INC.




DWG. # CW4C072810-DRA-ST


REV -

NOTES

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS FAN/CASING SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. -*APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]



FACE B



FACE A

SHIPPING WEIGHT 34120 lbs+ [15480] kg+ OPERATING WEIGHT 44420 lbs+ [20150] kg+ HEAVIEST SECTION WEIGHT 14870 lbs+ [6745] kg+ NO. OF SHIPPING SECTIONS 4 DRAWN BY: **JLG**