

UNIT	CLOSED CIRCUIT COOLER			DWG. #	CW4C071806-DRA-ST	REV.	-
MODEL #	eco-ATWB 7-3I18	SCALE NTS		SERIAL #		DATE	2/6/2026

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS FAN/CASING SECTION
3. MPT DENOTES MALE PIPE THREAD
FPT DENOTES FEMALE PIPE THREAD
BFW DENOTES BEVELED FOR WELDING
GVD DENOTES GROOVED
FLG DENOTES FLANGE
PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE
ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. -*APPROXIMATE DIMENSIONS DO NOT USE
FOR PRE-FABRICATION OF CONNECTING
PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO
RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]



DWG. # CW1C071806 DBA ST

REV.

SERIAL #


DATE 2/6/2026

FACE C




FACE B

PLAN VIEW



FACE B



FACE A

SHIPPING WEIGHT 16460 lbs+ [7470] kg+ OPERATING WEIGHT 21750 lbs+ [9870] kg+ HEAVIEST SECTION WEIGHT 13440 lbs+ [6100] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: TAM