UNIT CLOSED CIRCUIT COOLER			EV/AB	CO T	NC ev	DV DV	/G. # CW4C071808-DRA-ST	REV.	
MODEL #	eco-ATWB 7-4J18	SCALE NTS	T EVAP	CO, 1	NC. Ev	SEI	RIAL #	DATE _{12/13/2025}	
2. HÉAVIE 3. MPT DE FPT DE BFW DI GVD DE FLG DE PE DEN 4. +UNIT \ ACCES 5. MAKE-\ 20 psi M 6. *-APPR FOR PR FOR PR 7. 3/4" [19 RECOM	N MOTOR LOCATION ST SECTION IS FAN/CASIENOTES MALE PIPE THRE NOTES FEMALE PIPE THIS ENOTES BEVELED FOR WENOTES GROOVED NOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLUSORIES (SEE ACCESSOR JP WATER PRESSURE MIN [137 kPa], 50 psi MAX [30 OXIMATE DIMENSIONS DIRE-FABRICATION OF CON mm] DIA. MOUNTING HOLMMENDED STEEL SUPPOR SIONS LISTED AS FOLLOW ENGLISH FT-IN METRIC [mm]	AD READ //ELDING JDE Y DRAWINGS) 344 KPa] O NOT USE NECTING ES. REFER TO RT DRAWING.		FAS PLAN VI	CE B EW	ACCESS DOOR	CE C ACCES ACCES CE A	FACE D	
2" [50] M MAKE- 2" [50] M DR/ T1-11 [58	2'-3" * (2) 4" [100] BFW [686] * (2) 4" [100] BFW APT	1/4" *	2'-11 3/8" [899] + 1'-10 7/8" *		1'-2" [356]				
ָּרָ זָ	3"	'	3" [80] MPT OVERFLOW	1'-4 7/ [429	8"		3'-0" 486]		
		CE B		FACE A					
SHIPPING 19610 lbs+ [8895] kg+ WEIGHT		OPERATING WEIGHT 25640 lbs+ [11635] kg+	HEAVIEST SECTION WEIGHT	16590 lbs+ [7530] kg+	NO. OF SHIPPING SECTIONS 2	DRAWN BY: TAM		