



UNIT	CLOSED CIRCUIT COOLER
MODEL #	eco-ATWB 7-3J24

EVAPCO, INC. 

DWG. #	CW4C072406-DRA-ST	REV.	-
SERIAL #		DATE	2/5/2026

NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS FAN/CASING SECTION
3. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. *APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:
ENGLISH FT-IN
METRIC [mm]



SHIPPING
WEIGHT

21820 lbs+ [9900] kg+

OPERATING
WEIGHT

28800 lbs+ [13065] kg+

HEAVIEST SECTION
WEIGHT

9010 lbs+ [4090] kg+

NO. OF SHIPPING SECTIONS
4

DRAWN BY: TAM