

UNIT	CLOSED CIRCUIT COOLER	
MODEL #	eco-ATWB 14-6H18	SCALE NTS




DWG. #	CW4C141812-DRA-ST	REV. -
SERIAL #		DATE 2/16/2026


NOTES:

1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS FAN/CASING SECTION
3. MPT DENOTES MALE PIPE THREAD
- FPT DENOTES FEMALE PIPE THREAD
- BFW DENOTES BEVELED FOR WELDING
- GVD DENOTES GROOVED
- FLG DENOTES FLANGE
- PE DENOTES PLAIN END
4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
5. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
6. \*APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING
7. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
8. DIMENSIONS LISTED AS FOLLOWS:

ENGLISH FT-IN  
METRIC [mm]



**FACE B**



**FACE A**

HEAVIEST SECTION  
WEIGHT

22170 lbs+ [10060] kg+

NO. OF SHIPPING SECTIONS

4

DRAWN BY: TAM

SHIPPING  
WEIGHT

50380 lbs+ [22855] kg+

OPERATING  
WEIGHT

65420 lbs+ [29675] kg+