CLOSED CIRCUIT COOLER					<b>TNI</b>	over o		OWG. # CW4C141406-DRB-ST	REV _
MODEL#	eco-ATWB 14-3J14	SCALE NTS	t	VAPCO,	INC.	Evast		SERIAL #	DATE: 11/14/2025
2. HEAVI 3. MPT D FPT DE BFW D GVD D FLG DE 4. +UNIT ACCES 5. MAKE- 20 psi I FOR P PIPING 7. 3/4" [19 RECOI	AN MOTOR LOCATION EST SECTION IS FAN/CASI ENOTES MALE PIPE THRE, ENOTES FEMALE PIPE THE DENOTES BEVELED FOR W DENOTES FLANGE NOTES PLAIN END WEIGHT DOES NOT INCLU ESCORIES (SEE ACCESSOR) UP WATER PRESSURE MIN [137 kPa], 50 psi MAX [3 ROXIMATE DIMENSIONS DO RE-FABRICATION OF CONIC DEMM] DIA. MOUNTING HOLE MMENDED STEEL SUPPOR ISIONS LISTED AS FOLLOW ENGLISH FT-IN METRIC [mm]	AD READ /ELDING  JDE Y DRAWINGS)  344 kPa] O NOT USE NECTING  ES. REFER TO RT DRAWING.				FACE B PLAN VIEW	ACCE	FACE C  (M)  ACCESS DOOR  SS DOOR  (M)  FACE A	FACE D
1'-7 1/2" 1'-11	(4) 4* [100] BFW	"	FLUID IN	1'-10 7/8" * [581]  2'-11 3/8" [899]  (M)  4'-0 7/8" [1241]  12'-6 1/2" [  5 1/4" [133] *  5'-6 1/4" [1683]  -1'-3" [381]  (2) 3" [80] MPT  OVERFLOW	3822]	(4) 1/2" [' FPT VE 1'-5 1, [435	15] NT	13'-11 3/4" [4261]	
FACE B									Industrial Control
SHIPPING WEIGHT	24980 lbs+ [11335] kg-	OPERAT WEIGH	TING HT	2980 lbs+ [14960] kg+	HEAVIEST SECTI WEIGHT	<sup>ON</sup> 10300 lb	os+ [4675] kg+	NO. OF SHIPPING SECTIONS 4	DRAWN BY: JLG