EVAPCO, INC. evapeo N.T.S. UNIT MODEL # SERIAL # REV. CLOSED CIRCUIT COOLER eco-ATWB-H 12-2K14-Z-U22 EGH1214MR-DRC-SF 11/2/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 2. HÉAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD 7. * - APPROXIMATE DIMENSIONS DO FPT DENOTES FEMALE PIPE THREAD NOT USE FOR PRE-FABRICATION BFW DENOTES BEVELED FOR WELDING OF CONNECTING PIPING. **GVD DENOTES GROOVED** FLG DENOTES FLANGE +UNIT WEIGHT DOES NOT INCLUDE FACE 2 ACCESSORIES (SEE ACCESSORY **PLAN VIEW** DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 45 [1142] - FACE 1 ⁷ [178] (2) 1/2 [15] FPT VENT (2) 4 [100] BFW (M) (4) INLET 5 1/2 CROSSOVER **PIPING** 33 1/2 [851] VENT LOCATION (2) 1/2 [15] FPT VENT 83 9/32 13 3/4 207 7/8 **ACCESS DOORS** (2) 4 [100] BFW ÒÚTLĒT 19 1/4 [489] 5 7/8 [149] 2 [50] MPT 34 1/4 870] 68 1/8 [1730] MĀKĒ-UP (2) 1/2 [15] FPT 25 1/4 [641] CROSSOVER DRAIN 17 [432] 3 [80] MPT 3 5/8 [92] DRAIN 3 [80] MPT 5 1/4 [133] OVERFLOW 86 [2184] FACE 1 11'-10" [3607] FACE 2 NO. OF SHIPPING SECTIONS DRAWN BY: **SHIPPING** OPERATING HEAVIEST SECTION SFR 14030 lbs+ [6365] kg+ 20210 lbs+ [9170] kg+ 29320 lbs+ [13300] kg+ WEIGHT WEIGHT WEIGHT