## EVAPCO, INC. MODEL # N.T.S. UNIT SERIAL # EGH1220MR-DRB-ST CLOSED CIRCUIT COOLER eco-ATWB-H 12-2N20-U22 11/4/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 6. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH IN** 2. HÉAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD [METRIC] [mm] FPT DENOTES FEMALE PIPE THREAD 7. \* - APPROXIMATE DIMENSIONS DO BFW DENOTES BEVELED FOR WELDING NOT USE FOR PRE-FABRICATION 4. +UNIT WEIGHT DOES NOT INCLUDE OF CONNECTING PIPING. ACCESSORIES (SEE ACCESSORY FACE 2 DRAWINGS) **PLAN VIEW** 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] FACE 1 69 3/8 1762 ] 45 [ 1142 ] <del>-</del> . 7 [ 179 ] (2) 1/2 [15] FPT VENT 56 1/4 [ 1427 ] (2) 4 [100] BFW 5 1/2 INLET [140] **CROSSOVER PIPING** 36 3/8 [ 922 ] 33 1/2 36 3/8 <sub>-</sub> 851 ] [ 922 ] 13 3/4 83 9/32 213 7/8 [349] [2115] **ACCESS** [5432] **DOORS** (2) 4 [100] BFW OUTLET 5 7/8 [ 149 ] 2 [50] MPT 74 1/8 [ 1883 ] MAKE-UP 25 1/4 [ 641 ] 3 [80] MPT 17 [ 432 ] 4 1/4 [ 108 ] 3 5/8 [ 92 ] DRAIN 19 1/4 [ 489 ] 20'-0" [ 6096 ] 5 1/4 [ 133 ] 3 [80] MPT 86 [ 2184 ] **OVERFLOW** FACE 1 11'-10" 3607 FACE 2 SHIPPING OPERATING NO. OF SHIPPING SECTIONS DRAWN BY: HEAVIEST SECTION SFR 28060 lbs+ [12730] kg+ 41030 lbs+ [18615] kg+ 19470 lbs+ [8830] kg+ WEIGHT WEIGHT WEIGHT