

# EVAPCO, INC.




|      |                       |                                     |                 |                            |           |                  |          |
|------|-----------------------|-------------------------------------|-----------------|----------------------------|-----------|------------------|----------|
| UNIT | CLOSED CIRCUIT COOLER | MODEL #<br>eco-ATWB-H 12-2M14-Z-U22 | SCALE<br>N.T.S. | DWG. #<br>EGH1214MR-DRC-SF | REV.<br>- | DATE<br>9/8/2025 | SERIAL # |
|------|-----------------------|-------------------------------------|-----------------|----------------------------|-----------|------------------|----------|

## NOTES:


1. (M)- FAN MOTOR LOCATION
2. HEAVIEST SECTION IS COIL SECTION
3. MPT DENOTES MALE PIPE THREAD  
FPT DENOTES FEMALE PIPE THREAD  
BFW DENOTES BEVELED FOR WELDING  
GVD DENOTES GROOVED  
FLG DENOTES FLANGE
4. +UNIT WEIGHT DOES NOT INCLUDE  
ACCESSORIES (SEE ACCESSORY  
DRAWINGS)
5. MAKE-UP WATER PRESSURE  
20 psi MIN [137 kPa], 50 psi MAX [344 kPa]

6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER  
TO RECOMMENDED STEEL SUPPORT DRAWING.
7. \* - APPROXIMATE DIMENSIONS DO  
NOT USE FOR PRE-FABRICATION  
OF CONNECTING PIPING.

**FACE 2  
PLAN VIEW**



**FACE 1**



**FACE 2**

**FACE 1**

|                 |                       |                  |                        |                         |                       |                          |   |           |     |
|-----------------|-----------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|-----------|-----|
| SHIPPING WEIGHT | 20290 lbs+ [9205] kg+ | OPERATING WEIGHT | 29400 lbs+ [13340] kg+ | HEAVIEST SECTION WEIGHT | 14030 lbs+ [6365] kg+ | NO. OF SHIPPING SECTIONS | 3 | DRAWN BY: | SFR |
|-----------------|-----------------------|------------------|------------------------|-------------------------|-----------------------|--------------------------|---|-----------|-----|