EVAPCO, INC. N.T.S. EGH1212MR-DRB-ST eco-ATWB-H 12-4M12-U44

NOTES:

WEIGHT

UNIT


- 1. (M)- FAN MOTOR LOCATION
- 2. HÉAVIEST SECTION IS COIL SECTION
- 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING

CLOSED CIRCUIT COOLER

- 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS)
- 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa]
- 6. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH IN**

MODEL #

- [METRIC] [mm]
- 7. * APPROXIMATE DIMENSIONS DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.




DATE


11/6/2025

SERIAL #

FACE 1



WEIGHT



NO. OF SHIPPING SECTIONS

20470 lbs+ [9285] kg+

WEIGHT

DRAWN BY:

SFR