EVAPCO, INC.



N.T.S. UNIT MODEL # REV. DATE SERIAL # EGH0909MR-DRB-ST CLOSED CIRCUIT COOLER eco-ATWB-H 9-4K9-U22 12/7/2025 NOTES: (1) 1. (M)- FAN MOTOR LOCATION 6. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN 2. HÉAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD [METRIC] [mm] FPT DENOTES FEMALE PIPE THREAD 7. * - APPROXIMATE DIMENSIONS DO BFW DENOTES BEVELED FOR WELDING NOT USE FOR PRE-FABRICATION 4. +UNIT WEIGHT DOES NOT INCLUDE OF CONNECTING PIPING. ACCESSORIES (SEE ACCESSORY FACE 2 DRAWINGS) 5. MAKE-UP WATER PRESSURE **PLAN VIEW** 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] FACE 1 48 5/8 [1233] 35 1/8 - 21 3/8 [543] (2) 1/2 [15] FPT VENT 52 7/8 [1341] (2) 4 [100] BFW INLET 5 1/2 [140] **CROSSOVER PIPING** 33 1/2 26 1/2 _ [851] 203 8 249/400 27 26 1/2 [672] [2491] [5156] **ACCESS** [686] **DOORS** (2) 4 [100] BFW OUTLET 2 [50] MPT MAKE-UP 5 7/8 [149] 51 3/4 [1314] 23 1/8 [587] 15 5/8 [397] 4 1/4 [108] 15 [381] 3 [76] 3 [80] MPT 5 1/4 [133] 8'-11 1/2" **OVERFLOW** [2730] FACE 1 67 1/2 2 [50] MPT [1714] DRAIN 8'-5 1/2" 2578] FACE 2 SHIPPING OPERATING NO. OF SHIPPING SECTIONS DRAWN BY: HEAVIEST SECTION SFR 13770 lbs+ [6250] kg+ 18150 lbs+ [8235] kg+ 10160 lbs+ [4610] kg+ WEIGHT WEIGHT WEIGHT