EVAPCO, INC. MODEL # N.T.S. UNIT SERIAL # EGHTM1802-DRB-ST CLOSED CIRCUIT COOLER eco-ATWB-H 10-1L18-U34 8/25/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 6. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH IN** 2. HÉAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD [METRIC] [mm] FPT DENOTES FEMALE PIPE THREAD 7. * - APPROXIMATE DIMENSIONS DO BFW DENOTES BEVELED FOR WELDING NOT USE FOR PRE-FABRICATION 4. +UNIT WEIGHT DOES NOT INCLUDE OF CONNECTING PIPING. ACCESSORIES (SEE ACCESSORY FACE 2 DRAWINGS) **PLAN VIEW** 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] FACE 1 57 [1448] 39 [992] - (2) 1/2 [15] FPT VENT 56 1/4 [1427] (1) (2) 4 [100] BFW 6 7/8 INLET [175] **CROSSOVER PIPING** 22 1/2 [573] 33 1/2 [851] 38 1/2 [979] 75 1/32 193 5/8 [1906] 5 1/2 [4918] [140] **ACCESS** (2) 4 [100] BFW **DOORS** OUTLET 5 7/8 2 [50] MPT 62 1/8 [1578] [149] MAKE-UP 25 1/4 [641] 16 7/8 [429] 3 [80] MPT 4 1/4 [108] 3 5/8 ₂ [92] DRAIN 3 [80] MPT 19 1/8 18'-0" 5 1/4 [133] **OVERFLOW** [486] [5486] 71 3/4 FACE 1 9'-9 3/4" 2991 FACE 2 SHIPPING OPERATING NO. OF SHIPPING SECTIONS DRAWN BY: HEAVIEST SECTION SFR 20610 lbs+ [9350] kg+ 28540 lbs+ [12950] kg+ 12460 lbs+ [5650] kg+ WEIGHT WEIGHT WEIGHT