## EVAPCO, INC.

UNIT MODEL # SERIAL # N.T.S. EGH241802-DRD-ST CLOSED CIRCUIT COOLER eco-ATWB-H 24-1M18-U34 7/12/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 6. DIMENSIONS LISTED AS FOLLOWS: **ENGLISH IN** 2. HÉAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD [METRIC] [mm] FPT DENOTES FEMALE PIPE THREAD 7. \* - APPROXIMATE DIMENSIONS DO BFW DENOTES BEVELED FOR WELDING NOT USE FOR PRE-FABRICATION 4. +UNIT WEIGHT DOES NOT INCLUDE OF CONNECTING PIPING. ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] FACE 2 **PLAN VIEW** 24'-1 1/8" [ 7344 ] 69 3/8 [ 1762 ] FACE 1 27 5/8 \* 702 ] 7 [ 178 ] (4) 1/2 [15] FPT VENT -(4) 4 [100] BFW INLET 56 1/4 [ 1427 ] (11) CROSSOVER -6 7/8 113 3/4 \* **PIPING** 2888] [175] **ACCESS** 44 3/8 \* 1126 ] 33 1/2 851 ] **DOORS** 75 1/32 5 1/2 (4) 4 [100] BFW [1906] 229 5/8 [140] OUTLET [5832] 5 7/8 [ 149 ] 98 1/8 [ 2492 ] 25 1/4 [ 641 ] 5 1/4 [ 133 ] 3 5/8 [ [ 92 ] [ 432 ] 4 1/4 (2) 3 [80] MPT (2) 2 [50] MPT 19 [ 483 ] [ 108 ] **OVERFLOW** 56 [ 1422 ] [ 5486 ] MAKE-UP (2) 3 [80] MPT FACE 1 [ 3607 ] DRAIN FACE 2 SHIPPING OPERATING HEAVIEST SECTION NO. OF SHIPPING SECTIONS DRAWN BY: SFR 43460 lbs+ [19715] kg+ 64620 lbs+ [29315] kg+ 14060 lbs+ [6380] kg+ WEIGHT WEIGHT WEIGHT