EVAPCO, INC.



UNIT MODEL # SERIAL # REV. N.T.S. EGH2414MR-DRE-ST 10/26/2025 CLOSED CIRCUIT COOLER eco-ATWB-H 24-4M14-U22 NOTES: 1. (M)- FAN MOTOR LOCATION 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER 2. HÉAVIEST SECTION IS COIL SECTION TO RECOMMENDED STEEL SUPPORT DRAWING. 3. MPT DENOTES MALE PIPE THREAD 7. * - APPROXIMATE DIMENSIONS DO FPT DENOTES FEMALE PIPE THREAD NOT USE FOR PRE-FABRICATION BFW DENOTES BEVELED FOR WELDING OF CONNECTING PIPING. **GVD DENOTES GROOVED** FLG DENOTES FLANGE +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE FACE 2 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] **PLAN VIEW** FACE 1 5 1/8 [130] 27 5/8 702] 7 [178] (4) 1/2 [15] FPT VENT (4) 4 [100] BFW 56 1/4 (11) (M) CROSSOVER ÌNLET 51/2 -**PIPING ACCESS** 105 3/4 * 2684] 33 1/2 851 **DOORS** 30 3/4 100 9/32 36 3/8 * [922] 242 7/8 (4) 4 [100] BFW 5 7/8 * [149] ÒÚTLĒT 86 1/8 [2188] 25 1/4 [641] 5 1/4 [133] 3 5/8 [92] [432] 4 1/4 [108] (2) 3 [80] MPT (2) 2 [50] MPT **OVERFLOW** 4261] MAKE-UP 142 [3607] (2) 3 [80] MPT FACE 1 DRAIN FACE 2 OPERATING NO. OF SHIPPING SECTIONS DRAWN BY: **SHIPPING** HEAVIEST SECTION SFR 21500 lbs+ [9755] kg+ 55520 lbs+ [25185] kg+ 77540 lbs+ [35175] kg+ WEIGHT WEIGHT WEIGHT