## EVAPCO, INC. evapco N.T.S. UNIT MODEL # SERIAL # CLOSED CIRCUIT COOLER eco-ATWB-H 12-4M14-Z-U22 EGH1214MR-DRC-SF 11/6/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 2. HÉAVIEST SECTION IS COIL SECTION 3. MPT DENOTES MALE PIPE THREAD 7. \* - APPROXIMATE DIMENSIONS DO FPT DENOTES FEMALE PIPE THREAD NOT USE FOR PRE-FABRICATION BFW DENOTES BEVELED FOR WELDING OF CONNECTING PIPING. **GVD DENOTES GROOVED** FLG DENOTES FLANGE +UNIT WEIGHT DOES NOT INCLUDE FACE 2 ACCESSORIES (SEE ACCESSORY **PLAN VIEW** DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 45 [ 1142 ] <del>-</del> FACE 1 <sup>7</sup> [ 178 ] (2) 1/2 [15] FPT VENT (2) 4 [100] BFW (M) (4) INLET 5 1/2 CROSSOVER **PIPING** 33 1/2 [ 851 ] VENT LOCATION (2) 1/2 [15] FPT VENT 100 9/32 30 3/4 224 7/8 **ACCESS DOORS** (2) 4 [100] BFW ÒÚTLĒT 19 1/4 [ 489 ] 5 7/8 [ 149 ] 2 [50] MPT 34 1/4 870 ] 68 1/8 [ 1730 ] MĀKĒ-UP (2) 1/2 [15] FPT 25 1/4 [ 641 ] CROSSOVER DRAIN 17 [ 432 ] 3 [80] MPT 3 5/8 [ 92 ] DRAIN 3 [80] MPT 5 1/4 [ 133 ] OVERFLOW 86 [ 2184 ] FACE 1 11'-10" [ 3607 ] FACE 2 NO. OF SHIPPING SECTIONS DRAWN BY: **SHIPPING** OPERATING HEAVIEST SECTION SFR 21500 lbs+ [9755] kg+ 27760 lbs+ [12595] kg+ 38770 lbs+ [17590] kg+ WEIGHT WEIGHT WEIGHT