EVAPCO, INC.



UNIT MODEL # SERIAL # REV. N.T.S. TLETM1236-DRA-ST **COOLING TOWER** LSTE-10112U 12/13/2025 NOTES: 1. (M)- FAN MOTOR LOCATION 2. HÉAVIEST SECTION IS LOWER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FOR VICTAULIC 4. +UNIT WEIGHT DOES NOT INCLUDE FACE 1 9'-9' 3/4" ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] **PLAN VIEW** 6. 3/4" [19mm] DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm] 11'-11 3/4" 3651] FACE 2 1 1/2 [39] 117 3/4 [2991] 71 7/8 [1826] 11 5/8 ∠8 [200] BFW/GVD [297] **INLET** 77 7/8 [1979] (2) ACCESS DOOR -15'-3/8" [4583] 2 [50] MPT -4 [100] MPT 102 1/2 MAKE-UP OVERFLOW [2604] 31 3/8 [797] <u>•</u> <u>↓</u> 24 <u>▼</u> [610] 11'-11 3/4" 3651] 7 5/8 1 7/8 [48] [194] 3 5/8 [92] 7 1/8 _ 17 5/8 FACE 2 [181] [448] 31 3/4 3 [80] MPT [806] DRAIN 37 1/4 [946] 8 [200] BFW/GVD 9'-9 3/4" [2991] OUTLET FACE 1 SHIPPING OPERATING NO. OF SHIPPING SECTIONS HEAVIEST SECTION 8200 lbs+ [3719] kg+ 14110 lbs+ [6400] kg+ 5020 lbs+ [2277] kg+ 2 WEIGHT WEIGHT WEIGHT