COOLING TOWER	EVADCO	EVAPCO, INC.		DWG. # TV08124F-DRJ-ST	REV.
DDEL # LPT-8812U SCALE	EVAPCC	), TIAC.	evapco	SERIAL #	DATE 12/4/2025
OTES:  . (M)- FAN MOTOR LOCATION  . MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED FLG DENOTES FLANGE  . + UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE SEPARATE DRAWINGS FOR ACCESSORIES)  . 3/4" DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING  . MAKE-UP WATER PRESSURE-20 psi MIN, 50 psi MAX  . DIMENSIONS LISTED AS FOLLOWS: ENGLISH FT-IN [METRIC] MM		FACE B PLAN VIEW		FACE A	FACE D
3'-11" 8" [200] 8 INLET  8" [200] BFW/ OUT  7 1/4" [184]  7 1/4" [1195]  7'-10 1 [239]  FACE	8'-5/8" [2454]  GVD LET  2 5/8"   1'-8 1/8"   83/4"   222]	2 5/8" [ 67 ] 8'-11 1/2" [ 2730 ]	ACCESS DOOR  2" [50] MPT DRAIN  3" [75] MPT OVERFLOW  7'-11 7/8" [ 2435 ] 8'-6 7/8" [ 2613 ] 11'-5 3/4" [ 3499 ]	ACCESS DOOR	6'-7 3/4" [2026]