UNIT COOLING TOWER	FVADCO INC Evapco DWG. # AX122220-DRB-ST -
MODEL # SCALE AXS 12-22O22	EVAPCO, INC. EVAPCO, INC. SERIAL # AX122220-DRB-ST - 12/8/2025
NOTES: 1. (M)- FAN MOTOR LOCATION 2. HEAVIEST SECTION IS UPPER SECTION 3. MPT DENOTES MALE PIPE THREAD FPT DENOTES FEMALE PIPE THREAD BFW DENOTES BEVELED FOR WELDING GVD DENOTES GROOVED 4. +UNIT WEIGHT DOES NOT INCLUDE ACCESSORIES (SEE ACCESSORY DRAWINGS) 5. MAKE-UP WATER PRESSURE 20 psi MIN [137 kPa], 50 psi MAX [344 kPa] 6. 3/4" DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING. 7. DIMENSIONS LISTED AS FOLLOWS: ENGLISH IN [METRIC] [mm]	FACE B PLAN VIEW 1
7" [178]	
11'-10"	2'-5 3/4" 12" [300] 9'-3" 10'-1" 10'-1" 10'-1" 11'-4 1/2" 11'-4 1/2" 13467]
FACE B	3 7/8" [6934] [6934]
SHIPPING WEIGHT 19360 lbs+ [8785] kg+	OPERATING WEIGHT 40310 lbs+ [18285] kg+ HEAVIEST SECTION WEIGHT 10910 lbs+ [4950] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: JLM