UNIT	COOLING TOWER			NC evapco	DWG. # AX142409-DRA-ST	REV.
MODEL #	AXS 14-11P24	SCALE	EVAPCO, I	INC.	SERIAL #	DATE 12/8/2025
2. MPT DEN FPT DEN BFW DEN GVD DEN 3. +UNIT W ACCESS 4. MAKE-UF 20 psi MII 5. 3/4" DIA. RECOMM	MOTOR LOCATION IOTES MALE PIPE THREAD OTES FEMALE PIPE THREAD OTES FEMALE PIPE THREAD NOTES BEVELED FOR WELDIN IOTES GROOVED EIGHT DOES NOT INCLUDE ORIES (SEE ACCESSORY DRAP WATER PRESSURE N (137 kPa), 50 psi MAX (344 kP MOUNTING HOLES. REFER TO IENDED STEEL SUPPORT DRAP ONS LISTED AS FOLLOWS: EN	AWINGS) Pa] O AWING.	FACE B PLAN VIEW 6'-11 5/8' [2124]	ACCESS DO	(2) 15: INI FA!	10" [250] ASME 0 BOLT PATTERN LET CE D
7" [178] ¬				9 5/8" FACE A	<u>A</u>	
	13'-11 1 [4248]		11'-4 1/4" [3461] 37/8" [98] 3/8" [91/2" [241] 1'-6 7/8" [479] 2'-3 1/4" [692]	ACCESS DOOR	10'-3" [3124] 11'-1" [3378] 12'-4 1/2" [3772]	' [80] MPT AKE-UP ' [100] FPT VERFLOW ' [100] FPT RAIN
SHIPPING WEIGHT	15000 lbs+ [6805] kg	ODEDA	TING 32920 lbs+ [14935] kg+	HEAVIEST SECTION WEIGHT 15000 lbs+ [6805] I	Luc of curpous of office and	RAWN BY: SLR
3,2,3,11	1	- WEIG		1 10000	<u>- </u>	