UNIT	COOLING TOWER	FVAPCO INC evapco DWG. # AX142420-DRA-ST REV.
MODEL #	S 14-22R24	EVAPCO, INC. Evapco SERIAL # DATE 12/7/2025
3. MPT DENOTI FPT DENOTE BFW DENOT GVD DENOTI 4. +UNIT WEIGI ACCESSORII 5. MAKE-UP W/ 20 psi MIN [13 6. 3/4" DIA. MOI RECOMMENI	FOR LOCATION ECTION IS UPPER SECTION ES MALE PIPE THREAD ES FEMALE PIPE THREAD ES BEVELED FOR WELDING ES GROOVED HT DOES NOT INCLUDE ES (SEE ACCESSORY DRAWINGS) ATER PRESSURE 57 KPAJ, 50 psi MAX [344 kPa] JINTING HOLES. REFER TO DED STEEL SUPPORT DRAWING. ELISTED AS FOLLOWS: ENGLISH [METRIC]	
	13'-11 1/4" [ 4248 ]  FACE B	11'-4 1/4" [ 3462 ]  11'-2 5/8" [ 3418 ]  - 3/8" [ 100] FPT OVERILOW  37/8"  4" [100] FPT OVERILOW  37/8"  14" [350] BFW/GVD OUTLET  11'-1" [ 3378 ] 12'-4 1/2" [ 3378 ] 12'-4 1/2" [ 33772 ] 12'-5 3/4"  FACE A
SHIPPING WEIGHT	24170 lbs+ [10965] kg+	OPERATING WEIGHT 50820 lbs+ [23055] kg+ HEAVIEST SECTION 14420 lbs+ [6545] kg+ NO. OF SHIPPING SECTIONS 2 DRAWN BY: SLR